

Installation and Assembly - Adjustable Extension Column for Jumbo Mounts



This product is intended for use with UL Listed products and must be installed by a qualified professional installer.

Maximum UL Load Capacity : 900 lbs. (408 kg.)

Models:
 ADJ0203
 ADJ0305
 ADJ0406
 ADJ0507
 ADJ0608
 ADJ006009
 ADJ0709
 ADJ0810
 ADJ0911
 ADJ1012
 ADJ012018
 ADJ018024

IMPORTANT! Read entire instruction sheet before beginning installation and assembly.

⚠ WARNING

- Installer must verify that the supporting surface will safely support four times the combined weight of all attached equipment and hardware.

- 1 Attach threaded end of adjuster tube (**B**) to threaded fitting in ceiling plate. Tighten securely aligning slot in end of adjuster tube (**B**) with one of the holes in the side of threaded fitting. Insert and tighten one M5 x .8 x 10mm phillips screw (**E**) to lock adjuster tube (**B**) to threaded fitting.

⚠ WARNING

- Adjuster tube (**B**) must be fully threaded (six or seven full turns) onto threaded fitting in ceiling plate and then locked with screw (**E**).

- 2 Slide extension pipe (**A**) over adjuster tube (**B**) to the desired height. Attach with one bolt (**F**) and lock nut (**G**).

- 3 Attach Jumbo Mount (horizontal support shown) to threaded end of extension pipe (**A**) using retaining collar and fiber washer. Tighten retaining collar securely aligning one of the holes in the side of retaining collar with slot in end of extension pipe (**A**). Insert and tighten one M5 x .8 x 10mm phillips screw to lock retaining collar to extension pipe (**A**).

⚠ WARNING

- Retaining collar must be fully threaded (six or seven full turns) onto extension pipe (**A**) and then locked with M5 x .8 x 10mm screw.

PARTS LIST

	part number	qty.	description
A	*	1	extension pipe
B	**	1	adjuster tube
E	520-9250	1	M5 x .8 x 10mm phil. screw
F	580-1022	1	M10 x 60mm carriage bolt
G	530-9402	1	M10 center lock nut
	* 2MD-55VS11D for ADJ0203		154-1025 for ADJ006009
	2MD-55VS12D for ADJ0305		2MD-55VS03W for ADJ0709
	2MD-55VS10D for ADJ0406		2MD-55VS08W for ADJ0810
	2MD-55VS01D for ADJ0507		2MD-55VS05W for ADJ0911
	2MD-55VS09D for ADJ0608		2MD-55VS06W for ADJ1012
			154-1032 for ADJ012018
			154-1034 for ADJ018024
	** 154-1003 for ADJ0203.		154-1004 for all other models.
	** 154-1028 for ADJ006009		
	** 154-1030 for ADJ012018		
	** 154-1030 for ADJ018024		

